


# UNIBLOCKER

## FEATURES

- UNIBLOCKER has a flexible high-torque blocker shaft.
- UNIBLOCKER comes with a unique swivel connector
- including a port for fiberoptic bronchoscopy while connected to the anesthesia circuit




### Swivel Connector

UNIBLOCKER is equipped with a movable swivel connector. This allows rotation of the circuit if the patient is moved. The swivel connector allows easy insertion of a fiberoptic bronchoscope.



## External chart

### Swivel Connector



### UNIBLOCKER [Adult and Pediatric]

### Torque Control Blocker

UNIBLOCKER shaft incorporates a metallic mesh which gives torque control. The mesh is radiopaque.



### Easy Removal

UNIBLOCKER is easily removed without disconnecting the swivel connector from the anesthesia circuit. Simply remove all the air from the cuff and disconnect the quick release connector.



## ORDERING INFORMATION

Reference No.	Size (Outler diameter Shaft)	Length	Cuff Length	Maximum Cuff Volume	Net Volume of Swivel connector	Length	Packaging
1203104	1.7mm (5Fr)	450mm	8mm	3mL	20.5mL	450mm	1 / box
1203105	3.0mm (9Fr)	665mm	22mm	8mL	20.5mL	665mm	

